

# X-Cite<sup>®</sup> 200DC

The Ultimate Combination  
of Optical Performance  
and Speed.

- DC lamp technology providing stable output
- Smooth 0 to 100% intensity adjustment for maximum control
- High speed internal shutter
- Auto-light guide detection to optimize performance and lifetime

The X-Cite<sup>®</sup> 200DC brings together the most valued X-Cite<sup>®</sup> features and delivers them in one system. Ideal for routine imaging and advanced applications requiring millisecond stability.



LUMEN DYNAMICS  
PUTTING YOU IN CONTROL

X-Cite<sup>®</sup>  
200DC

FEATURES	BENEFITS
DC lamp	Exceptional short and medium term intensity stability
Adjustable iris, 0-100%	Intensity control to avoid photobleaching and optimize illumination levels
Internal high speed shutter	Limits photobleaching and mechanical vibration transferred to microscope during automated imaging for better image quality
Liquid Light Guide	Superior illumination uniformity and elimination of heat transfer to microscope
Automatic Light Guide Detection	Ensures proper/complete insertion of light guide to optimize performance and extend lifetime
Pre-aligned 2000 hour lamp	Easy lamp replacement with no alignment required
Intelli-Lamp® Technology	Maintains optimum lamp temperature; Monitors lamp hours

## SPECIFICATIONS

Includes	Lamp module, liquid light guide with adaptor, foot pedal, grounded and shielded power cord, user guide (on CD), quick-start guide
Lamp	200W Mercury Vapor Short Arc, DC
Lamp Life	2000 hours guaranteed, 2500 hours typical
Adaptors	Compatible with microscopes from all major manufacturers
Filter	Bandpass, 340-800nm, non-removable
Shutter	Front panel button, foot pedal, TTL input/sync output Response time: 5-6 ms trigger to open/close (TTL)
Iris	ND (Neutral Density) mesh, manual dial control, continuous non-detent motion from 0-100%
Warm-up Period	4 minutes (typical)
Panel Controls	Power on/off, shutter open/close, manual iris adjustment dial
Panel Display	Accumulated lamp hours, status messages
Panel Status Indicators	Lamp on, shutter open, light guide insertion
Power Supply	Power Factor Corrected, Universal Input
Input Voltage	100-240VAC, 50/60Hz
Current	3.5A max at 120VAC, 2.0A max at 240VAC
Input Surge	50A max (cold start)
Fuse Rating	Dual fuse: each rated at F5.0A 250V, 5x20mm type
Dimensions	13.5" x 7" x 8" 34cm x 18cm x 20cm
Weight	10.8lbs / 4.9kg
Certifications	CE marked, certified to IEC, Canadian and US Standards
Warranty	1 year (excluding lamp and light guide)



**LUMEN DYNAMICS**  
PUTTING YOU IN CONTROL

2260 Argentia Road,  
Mississauga, Ontario,  
LSN 6H7 CANADA

[www.LDGI-XCite.com](http://www.LDGI-XCite.com)

Telephone: +1 905 821-2600  
Toll Free (USA and Canada): +1 800 668-8752  
Facsimile: +1 905 821-2055

[X-Cite@LDGI.com](mailto:X-Cite@LDGI.com)



Lumen Dynamics Group Inc. is certified under the globally recognized ISO 9001 Quality Management System and the ISO 14001 Environmental Management System. Our global customers can trust that Lumen Dynamics strives to be the best possible supplier in all aspects of our business.

X-Cite® and Intelli-Lamp® are registered trademarks of Lumen Dynamics Group Inc. All rights reserved.  
Background image supplied by Ludwig Eckl, Liebmann Optical Company Inc.

Lumen Dynamics has made every effort to ensure that the information contained in this specification sheet is accurate. However, we accept no responsibility for any errors or omissions, and we reserve the right to modify design, characteristics and products at any time without obligation. Contact Lumen Dynamics for prices and availability or to obtain the phone number of your local Lumen Dynamics representative.